



# Twin Clamping Two Hole Mounting Heavy Duty Copper Lug Connector

By Burndy  
Catalog # [QQA402N](#)



Copper Terminal, Heavy Duty, 2 Hole, 600-800 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 2 Screws.

## General

Connector Type	Duel Clamp
Installation Torque	500 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810326152

## Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	2.3125 in
Dimension - Height inch	2.31 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	173 mm
Dimension - Length Overall inch	6.81 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.63 in

## Conductor Related

Conductor - Copper Str Navy Size	650 (127) Navy;800 (127) Navy
Conductor - Copper Str Navy Size Range	650 (127) Navy-800 (127) Navy
Conductor - Copper Str Size	600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	600 kcmil-800 kcmil
Conductor Size	600-800 kcmil
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Str Navy-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	24
-----------------------	----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SA..005911-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-QQA402N-SPEC-EN | REV 1/2024