

Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # T146



Uninsulated Ring Terminal For 16 - 14 AWG.

Application

For Control Wiring And Other Standard Duty Applications

General

Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810722367
UPC 12 Digit	7818107223677

Dimensions

Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Diameter Max Size inch	0.08 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - L Length Overall mm	17
Dimension - Length Overall inch	0.66 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	#4 - #6
Dimension - Z inch	0.28 in

Conductor Related

Conductor Range	#20 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[3D Models - T146_MODEL-PDF](#)
[3D Models - T146_MODEL-IGES](#)
[3D Models - T146_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094154](#)

