

# Uninsulated Locking Fork Terminal For 16 - 14 AWG

By Burndy  
Catalog # T146LF



Uninsulated Locking Fork Terminal For 16 - 14 AWG.

## Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from copper alloy, permits many installation while maintaining proper spring retention of forks

## General

Connector Type	Locking Fork Terminal
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Snap Fork
Trade Name	HYLUG™
UPC	781810530788
UPC 12 Digit	7818105307888

## Dimensions

Dimension - Bolt Size fraction	#4 - #6
Dimension - L Length Overall mm	21
Dimension - Length Overall inch	0.81 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z (inch)	0.30 in

## Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50094175](#)