

SP10BG25, Vinyl Splice For 12 - 10 AWG

By Burndy
Catalog # [SP10BG25](#)



Vinyl Splice For 12 - 10 AWG.

Features

- Splices are constructed of pure electrolytic copper
- Long butted seam with deep V groove inner serrations for optimum conductivity, reliability, and holding power after crimping
- Designed for joining two wires securely
- Provides maximum conductivity, low resistance, and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105° C maximum

Application

For Accommodating A Broad Range Of 600 Volt Cables

General

Catalog Number	SP10BG25
Color Code	Yellow
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Temperature Rating	105° C
Trade Name	VINYLINK™
Type	SP
UPC	781810486276
UPC 12 Digit	7818104862766

Dimensions

Dimension - Diameter Max Size	0.26 in
Dimension - Length Overall	1.23 in
Dimension - Strip Length inch	21/64 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 - 10 AWG
Conductor Size	12 - 10 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10104489](#)
[Specifications - SP10BG25](#)



A Hubbell brand