



Vinyl Splice For 22 - 16 AWG

By Burndy
Catalog # SP16

Copper Splice, 22-16 AWG, 1" Splice Length, Vinyl Insulated, Tin Plated.



Features

- Manufactured from seamless electrolytic copper tubing to provide maximum conductivity and tensile strength in a high quality design with no seams to split
- Funnel entry for easy wire insertion
- Electro-tin plating provides durable, long lasting resistance to corrosion

Application

For Accommodating A Broad Range Of 600 Volt Cables

General

Color Code	Red
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	VINYLINK
Temperature Rating	105° C
Trade Name	VINYLINK™
Type	SP
UPC	781810714010
UPC 12 Digit	7818107140100

Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Diameter Max Size inch	0.14 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - Outside Diameter inch	0.15 in
Dimension - Strip Length inch	1/4 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Solid Size	20 ;18 AWG;17 AWG;16 AWG
Conductor - Copper Solid Size Range	20 -16 AWG
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG
Conductor - Copper Str Size Range	22 - 16 AWG
Conductor Size	22 - 16 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

- [3D Models - SP16_MODEL-IGES](#)
- [3D Models - SP16_MODEL-STEP](#)
- [3D Models - SP16_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_KTFBS_LineArt](#)
- [Sales Drawings - 50094190](#)



A proud member of the Hubbell Family.

