

Uninsulated Locking Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # T148LF



Uninsulated Locking Fork Terminal For 16 - 14 AWG.

Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from copper alloy, permits many installation while maintaining proper spring retention of forks

General

Connector Type	Locking Fork Terminal
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Snap Fork
Trade Name	HYLUG™
UPC	781810530795
UPC 12 Digit	7818105307955

Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	21
Dimension - Length Overall inch	0.83 in
Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#6 - #8
Dimension - Z (inch)	0.30 in

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094175](#)