

# T1014F, Uninsulated Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # T1014F



Uninsulated Fork Terminal For 12 - 10 AWG.

## Features

- Type T-F uninsulated fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork style permits rapid installation of the terminal under screw head without completely removing screw
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion

## Application

For Control Wiring And Other Standard Duty Applications

## General

Catalog Number	T1014F
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	T-F
UPC	781810722145
UPC 12 Digit	7818107221455

## Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - L Length Overall mm	25 mm

Dimension - Length Overall inch	1.00 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	1/4
Dimension - Z (inch)	0.39 in

## Conductor Related

Conductor - Copper Str Size	14 AWG;10 AWG (Str.);12 AWG (Sol.);10 AWG
Conductor - Copper Str Size Range	14 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_tfla](#)
- [Sales Drawings - 50094170](#)
- [Specifications - T1014F](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
BRDY-T1014F-SPEC-EN | REV 1/2025