

T108F, Uninsulated Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # T108F



Uninsulated Fork Terminal For 12 - 10 AWG.

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Control Wiring And Other Standard Duty Applications

General

Catalog Number	T108F
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	T-F
UPC	781810722060
UPC 12 Digit	7818107220600

Dimensions

Cable Insulation Diameter Maximum	0.12 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in

Dimension - Bolt Size fraction	#6 - #8
Dimension - Diameter Max Size inch	0.12 in
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - L Length Overall mm	20 mm
Dimension - Length Overall inch	0.80 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.27 in

Conductor Related

Conductor - Copper Str Size	14 AWG;10 AWG (Str.);12 AWG (Sol.);10 AWG
Conductor - Copper Str Size Range	14 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_tfla
Sales Drawings - 50094170
Specifications - T108F



©2024 Hubbell Incorporated. All rights reserved
BRDY-T108F-SPEC-EN | REV 10/2024