



## TN1014, Nylon Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # TN1014

Copper Terminal, Ring Tongue, 12-10 AWG, #12,1/4" Stud, 600  
Volts Max., Nylon Insulated, Funnel Entry, Tin Plated.



## Features

- Deep inner barrel serrations and smooth funnel entry provide excellent conductivity and pullout strength values with easy wire insertion
- Color-coded and clearly marked for quick easy wire size identification

## Application

For Heavy Duty Industrial, Utility And Military Power And Control-Circuit Applications

## General

Catalog Number	TN1014
Color Code	Yellow
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	Ring Tongue
UPC	781810734209

## Dimensions

Cable Insulation Diameter Maximum	0.21 in
Dimension - Bolt Size fraction	#12 - 1/4
Dimension - L Length Overall mm	34 mm
Dimension - Length Overall inch	1.32 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#12;1/4
Dimension - Z (inch)	0.37 in

## Electrical Ratings

Voltage - Maximum 600 V

## Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

## Product Assets

[3D Models - TN1014\\_MODEL-IGES](#)  
[3D Models - TN1014\\_MODEL-STEP](#)  
[3D Models - TN1014\\_MODEL-PDF](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_TN186\\_LineArt](#)  
[Sales Drawings - 50094155](#)  
[Specifications - TN1014](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-TN1014-SPEC-EN | REV 8/2024