



Nylon Block Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # TN106BF



Nylon Block Fork Terminal For 12 - 10 AWG.

Features

Permits rapid and easy installation of the terminal under the screw head without complete removal of the screw

Application

Power Connector

General

Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	Fork Tongue
UPC	781810524121

Dimensions

Dimension - Bolt Size fraction	#4 - #6
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	3/8
Dimension - Stud Size inch	#4;#5;#6
Dimension - Z (inch)	0.29 in

Conductor Related

Conductor Range	#10 AWG to #12 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	50

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_TN1010BF_LineArt](#)
[Sales Drawings - 50094182](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-TN106BF-SPEC-EN | REV 5/2024