

T1610LF, Uninsulated Locking Fork Terminal For 22 - 16 AWG

By Burndy
Catalog # T1610LF



Uninsulated Locking Fork Terminal For 22 - 16 AWG.

Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from copper alloy, permits many installation while maintaining proper spring retention of forks

General

Catalog Number	T1610LF
Connector Type	Locking Fork Terminal
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Snap Fork
Trade Name	HYLUG™
UPC	781810530818
UPC 12 Digit	7818105308188

Dimensions

Dimension - Bolt Size fraction	#8 - #10
Dimension - L Length Overall mm	21
Dimension - Length Overall inch	0.83 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	9/32 in

Dimension - Stud Size inch	#8 - #10
Dimension - Z (inch)	0.32 in

Conductor Related

Conductor Range	#22 AWG to #18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094175](#)
[Specifications - T1610LF](#)