

# TN108LF, Nylon Locking Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # TN108LF



Nylon Locking Fork Terminal For 12 - 10 AWG.

## Features

- Locking fork tongue design allows fast installation - screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

## Application

Power Connector

## General

Catalog Number	TN108LF
Connector Type	Locking Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Unplated
Sub Brand	HYDENT
Trade Name	INSULUG™
Type	TN
UPC	781810524152

## Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in

Dimension - Pad Width inch	0.33 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.29 in

## Conductor Related

Conductor Range	#10 AWG to #12 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_TN1010LF\\_LineArt](#)
- [Sales Drawings - 50094177](#)
- [Specifications - TN108LF](#)