

TN1414, Nylon Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # TN1414



Nylon Ring Terminal For 16 - 14 AWG.

Features

- Integral one-piece copper barrel / insulation grip and wire strain relief design for improved physical strength characteristics over a multi-piece design
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Brazed seam provides a stronger barrel design, minimizes any possible splitting and eliminates folding
- Deep inner barrel serrations and smooth funnel entry for excellent conductivity and pullout strength values along with the easy wire insertion
- Insulation is locked in place, will not twist off, maintaining proper dielectric values
- Electro-tin plated for durable, long lasting resistance to identification
- Ring tongue provides a secure termination under the screw head that cannot be removed without complete removal of the screw, allowing two or more terminals to be stacked on a common stud

Application

For Heavy Duty Industrial, Utility And Military Power And Control-Circuit Applications

General

Catalog Number	TN1414
Color Code	Blue
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	Ring Tongue

UPC 781810734605

Dimensions

Cable Insulation Diameter Maximum	0.153 in
Dimension - Bolt Size fraction	#12 - 1/4
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.08 in
Dimension - Pad Width inch	0.45 in
Dimension - Strip Length inch	7/32
Dimension - Stud Size inch	#12;1/4
Dimension - Z (inch)	0.43 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Range	#16 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[3D Models - TN1414_MODEL-STEP](#)
[3D Models - TN1414_MODEL-IGES](#)

[3D Models - TN1414_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TN186_LineArt](#)
[Sales Drawings - 50094155](#)
[Specifications - TN1414](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-TN1414-SPEC-EN | REV 10/2024