




TN106LF, Nylon Locking Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # TN106LF



Snap Fork Tongue, 12 AWG - 10 AWG.

Features

- Locking fork tongue design allows fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from copper alloy, permits many installations while maintaining proper spring retention of forks

Application

Power Connector

General

Catalog Number	TN106LF
Connector Type	Locking Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Unplated
Sub Brand	HYDENT
Trade Name	INSULUG™
Type	TN
UPC	781810524138

Dimensions

Dimension - Bolt Size fraction	#4 - #6
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	#4;#6
Dimension - Z (inch)	0.29 in

Conductor Related

Conductor Range	#10 AWG to #12 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TN1010LF_LineArt](#)
[Sales Drawings - 50094177](#)
[Specifications - TN106LF](#)



A Hubbell brand