



TN108BF, Nylon Block Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [TN108BF](#)

Nylon Block Fork Terminal For 12 - 10 AWG.

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

Power Connector

General

Catalog Number	TN108BF
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	Fork Tongue
UPC	781810524145

Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.33 in



Dimension - Strip Length inch	3/8
Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.29 in

Conductor Related

Conductor Range	#10 AWG to #12 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	50

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TN1010BF_LineArt](#)
[Sales Drawings - 50094182](#)
[Specifications - TN108BF](#)



A Hubbell brand