



## TN148BF, Nylon Block Fork Terminal For 16 - 14 AWG

By Burndy  
Catalog # TN148BF



Nylon Block Fork Terminal For 16 - 14 AWG.

### Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

### Application

Power Connector

### General

Catalog Number	TN148BF
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	Fork Tongue
UPC	781810524206

### Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	3/16
Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.30 in

### Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	100
Minimum Pack Quantity	100

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_TN1010BF\\_LineArt](#)
- [Sales Drawings - 50094182](#)
- [Specifications - TN148BF](#)