



Vinyl Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [TP1038](#)



Terminal-Polyvinylchloride Insulated, Ring Tongue, 12-10 Max. Insul.Dia. Accom.: .260 Color Code:Yellow, 3/8, 1.27 in L, .53 in W, 600 Volts Max., 105 Deg C Max.

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Color Code	Yellow
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810711446
UPC 12 Digit	7818107114466

Dimensions

Cable Insulation Diameter Maximum	0.26 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Bolt Size fraction	3/8
Dimension - Diameter Max Size inch	0.28 in
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.40 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.3 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	19/64 in
Dimension - Stud Size inch	3/8 in
Dimension - Z (inch)	0.45 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_TP1010_LineArt](#)
- [Sales Drawings - 50093722](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-TP1038-SPEC-EN | REV 5/2024