

TN184F, Nylon Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # TN184F

Nylon Fork Terminal For 22 - 18 AWG.



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

General

| | |
|----------------------------------|----------------------|
| Catalog Number | TN184F |
| Connector Type | Fork Terminal |
| Feature - Barrel Style | Shrouded |
| Insulation Type | Nylon |
| Material | Copper |
| Physical Attribute - Tongue Type | Fork |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | INSULUG™ |
| UPC | 781810530870 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Bolt Size fraction | #3 - #4 |
| Dimension - L Length Overall mm | 19 mm |
| Dimension - Length Overall inch | 0.75 in |
| Dimension - Pad Width inch | 0.23 in |
| Dimension - Strip Length inch | 7/32 |
| Dimension - Stud Size inch | #3;#4 |
| Dimension - Z (inch) | 0.24 in |

Conductor Related

| | |
|----------------|---|
| Conductor Size | 22 - 18 AWG |
| Conductor Type | <ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | UI |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - TN184F](#)