



TP1638, Vinyl Ring Terminal For 22 - 16 AWG

By Burndy
Catalog # TP1638

Vinyl Ring Terminal For 22 - 16 AWG.



Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Catalog Number	TP1638
Color Code	Red
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	COMPRESSION TERMINAL, VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810715444
UPC 12 Digit	7818107154444

Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Bolt Size fraction	3/8
Dimension - Diameter Max Size inch	0.15 in
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.15 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	13/64
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.45 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Solid Size	20 ;18 AWG;17 AWG;16 AWG
Conductor - Copper Solid Size Range	20 -16 AWG
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG
Conductor - Copper Str Size Range	20 AWG - 16 AWG
Conductor Size	22 - 16 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50093722](#)
[Specifications - TP1638](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-TP1638-SPEC-EN | REV 8/2024