

Vinyl Ring Terminal For 22 - 16 AWG

By Burndy
Catalog # TP164



Vinyl Ring Terminal For 22 - 16 AWG.

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Color Code	Red
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	COMPRESSION TERMINAL, VINYLUG
Trade Name	VINYLU TM
Type	Ring Tongue
UPC	781810714249
UPC 12 Digit	7818107142499

Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Bolt Size fraction	#3 - #4
Dimension - L Length Overall mm	18 mm
Dimension - Length Overall inch	0.71 in
Dimension - Pad Width inch	0.22 in
Dimension - Strip Length inch	13/64
Dimension - Stud Size inch	#3;#4
Dimension - Z inch	0.17 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	20 ;18 AWG;17 AWG;16 AWG
Conductor - Copper Solid Size Range	20 -16 AWG
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG
Conductor - Copper Str Size Range	20 AWG-16 AWG
Conductor Size	22 - 16 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[3D Models - TP164_MODEL-STEP](#)
[3D Models - TP164_MODEL-PDF](#)
[3D Models - TP164_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50093722](#)

