



TN184F, Nylon Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [TN184F](#)



Nylon Fork Terminal For 22 - 18 AWG.

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

General

Catalog Number	TN184F
Connector Type	Fork Terminal
Feature - Barrel Style	Shrouded
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	INSULUG™
UPC	781810530870

Dimensions

Dimension - Bolt Size fraction	#3 - #4
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in
Dimension - Pad Width inch	0.23 in
Dimension - Strip Length inch	7/32
Dimension - Stud Size inch	#3;#4
Dimension - Z (inch)	0.24 in

Conductor Related

Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">CU C Solid-SizeCU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - TN184F](#)



A Hubbell brand