

TP16516, Vinyl Ring Terminal For 22 - 16 AWG

By Burndy
Catalog # [TP16516](#)



Vinyl Ring Terminal For 22 - 16 AWG.

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Catalog Number	TP16516
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	Ring Tongue
UPC	781810524374
UPC 12 Digit	7818105243744

Dimensions

Dimension - Bolt Size fraction	5/16
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.11 in
Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	13/64
Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	5/16
Dimension - Z (inch)	0.41 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Size	22 - 16 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	50

Product Assets

[3D Models - TP16516_MODEL-PDF](#)
[3D Models - TP16516_MODEL-STEP](#)
[3D Models - TP16516_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TP1010_LineArt](#)
[Sales Drawings - 50093722](#)
[Specifications - TP16516](#)



A Hubbell brand