



Vinyl Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [TP186FBG25](#)



Vinyl Fork Terminal For 22 - 18 AWG.

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

General

Connector Type	Fork Terminal
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810486573
UPC 12 Digit	7818104865733

Dimensions

Dimension - Bolt Size fraction #22-#18

Conductor Related

Conductor Size 22 - 18 AWG
Conductor Type CU C Str-Size

Certifications And Compliance

Certification - CSA Approved Yes
Certification - ETL No
Certification - UL Recognized No
Certification - cULus No
Industry Standard(s) UL467
Standards - Industry UL486
Standards Met
Standards - RoHS Compliance CM
Status
UL Listed Yes

Logistics

Minimum Pack Quantity 5

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10104489](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-TP186FBG25-SPEC-EN | REV 5/2024