



## TN202F, Nylon Fork Terminal For 26 - 20 AWG

By Burndy  
Catalog # [TN202F](#)

Nylon Fork Terminal For 26 - 20 AWG.



## Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

## Application

Power Connector

## General

Catalog Number	TN202F
Color Code	Amber
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	TN-F
UPC	781810734919

## Dimensions

Cable Insulation Diameter Maximum	0.098 in
Dimension - Bolt Size fraction	#1 - #2
Dimension - L Length Overall mm	19 mm

Dimension - Length Overall inch	0.76 in
Dimension - Pad Width inch	0.18 in
Dimension - Strip Length inch	3/16
Dimension - Stud Size inch	#1;#2
Dimension - Z (inch)	0.24 in

## Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Size	20 AWG
Conductor - Copper Str Size Range	20 AWG
Conductor Range	#20 AWG to #26 AWG
Conductor Size	26 - 20 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_yaesfla](#)  
[Sales Drawings - 50094172](#)  
[Specifications - TN202F](#)

