



TN206F, Nylon Fork Terminal For 26 - 20 AWG

By Burndy
Catalog # [TN206F](#)

Nylon Fork Terminal For 26 - 20 AWG.



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

Power Connector

General

Catalog Number	TN206F
Color Code	Amber
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	TN-F
UPC	781810734957

Dimensions

Cable Insulation Diameter Maximum	0.098 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - L Length Overall mm	20 mm

Dimension - Length Overall inch	0.80 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	3/16
Dimension - Stud Size inch	#4;#5;#6
Dimension - Z (inch)	0.28 in

Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	20 AWG
Conductor - Copper Str Size Range	20 AWG
Conductor Range	#20 AWG to #26 AWG
Conductor Size	26 - 20 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_yaesfla](#)
[Sales Drawings - 50094172](#)
[Specifications - TN206F](#)

