

# Vinyl Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # [TP1014](#)



Copper Terminal, Ring Tongue, 12-10 AWG, 1/4" Stud, Vinyl Insulated, Tin Plated, Wire strip Length: 19/64".

## Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

## General

Catalog Number	TP1014
Color Code	Yellow
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810711040
UPC 12 Digit	7818107110400

## Dimensions

Cable Insulation Diameter Maximum	0.28 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.26 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	19/64 in
Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.40 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

## Product Assets

[3D Models - TP1014\\_MODEL-STEP](#)  
[3D Models - TP1014\\_MODEL-IGES](#)  
[3D Models - TP1014\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_TP1010\\_LineArt](#)  
[Sales Drawings - 50093722](#)

