

# TP1014F, Vinyl Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # TP1014F



Vinyl Fork Terminal For 12 - 10 AWG.

## Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

## General

Catalog Number	TP1014F
Color Code	Yellow
Connector Type	Fork Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Trade Name	VINYLUG™
UPC	621945047105
UPC 12 Digit	6219450471055

## Dimensions

Cable Insulation Diameter Maximum	0.26 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	13/50
Dimension - Hole Size inch	0.26 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.26 in
Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.46 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	100
Minimum Pack Quantity	50

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - TP1014F](#)