



UH133B, Substation Copper Bus Support, #6 AWG Str-500 kcmil, Cu Pipe Size: 1/8"-1/2" IPS, 3" Bolt Circle Dia, includes Base Mounting Hardware

By Burndy
Catalog # UHR133B



*Representative Image

Cast Cu Alloy Bus Support with Base Mounting Hardware, CU Str. Size: 6 AWG - 500 Kcmil, CU Pipe Size: 1/8"-1/2" IPS, 3 IN Bolt Circle Dia.

Application

Substation

General

Catalog Number	UHR133B
Connector Type	Bus Support
Fitting Type	Rigid Conduit
Hardware Type	Base mounting kit (w nuts)
Installation Torque	240 in-lb
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	1/2 X 1 1/2" Hot Dipped Steel Hex. Head Bolts
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810126592
UPC 12 Digit	7818101265922

Dimensions

Bolt Circle Diameter	3 in
Dimension - B Length inch	3.56 in
Dimension - G inch	1.75 in
Dimension - Height inch	3.00 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm

Conductor Related

Conductor - Connection Combination	Base to Tube or Cable
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	6 AWG-500 kcmil
Conductor - Copper Tube Std Size	1/8 IPS IPS;1/4 IPS IPS;3/8 IPS IPS;1/2 IPS IPS
Conductor - Copper Tube Std Size Range	1/8 IPS IPS-1/2 IPS IPS
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	8
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sa039220-01](#)
- [Specifications - UHR133B](#)