

## VP2828, V-Bolt Connector for Flex or Extra Flex Conductor

By Burndy  
Catalog # VP2828



1/0 STR. - 4/0 STR. GROOVE A GROOVE B.

### Features

- Type VP, Parallel Groove Clamp for Copper
- Multiple V-Bolt connector especially suited for flexible or extra flexible conductors
- Made of high strength, high conductivity copper
- Clamping elements accommodate a range of conductor sizes in either groove
- V-bolts provide high pressure and compress the conductor over long contact area
- Also suitable for jumper connections

### General

Catalog Number	VP2828
Connector Type	V-Bolt
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810013571

### Dimensions

Dimension - Height fraction	2-1/8 in
Dimension - Height inch	2.13 in
Dimension - Height mm	54.1 mm
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.75 in
Dimension - Width mm	44 mm

### Conductor Related

Conductor - Copper Str Size A	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size A Range	1/0 -4/0 AWG
Conductor - Copper Str Size B	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size B Range	1/0 -4/0 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

### Logistics

Minimum Pack Quantity	8
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_VP\\_PAR\\_CLAMP\\_LineArt](#)  
[Sales Drawings - 50004889](#)  
[Specifications - VP2828](#)