

TP106Z, Vinyl Flanged Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # TP106Z



Vinyl Flanged Fork Terminal For 12 - 10 AWG.

Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- The flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

General

Catalog Number	TP106Z
Color Code	Yellow
Connector Type	Flanged Fork Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Tin
Trade Name	VINYLUG™
Type	Flange Fork
UPC	781810710562
UPC 12 Digit	7818107105622

Dimensions

Cable Insulation Diameter Maximum	0.26 in
Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	0.99 in
Dimension - Pad Width inch	0.28 in

Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#6
Dimension - Z (inch)	0.26 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094185](#)
- [Specifications - TP106Z](#)
- [Specifications - BURNDY_TP106Z_Specsheet](#)