

TP108BF, Vinyl Block Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [TP108BF](#)



Vinyl Block Fork Terminal For 12 - 10 AWG.

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Catalog Number	TP108BF
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Tongue Type	Block Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	VINYLUG™
Type	Fork Tongue
UPC	781810524329
UPC 12 Digit	7818105243299

Dimensions

Cable Insulation Diameter Maximum	0.26 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	26 mm

Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.33 in
Dimension - Strip Length inch	19/64 in
Dimension - Stud Size inch	#6 - #8
Dimension - Z (inch)	0.29 in

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	50

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TP166BF_LineArt](#)
[Sales Drawings - 50094181](#)
[Specifications - TP108BF](#)