



WILEYBRAID24, Cu Braid , 76.00 IN L, 0.709 IN W, M6 or 1/4" Hardware NOT included

By Burndy
Catalog # [WILEYBRAID76](#)



WILEY Bonding Jumpers are perfect for tracker applications, galvanized steel, or anywhere a WEEB® washer is not required.

Features

Perfect for tracker applications, galvanized steel or anywhere a WEEB washer is not required

Application

The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.

General

Catalog Number WILEYBRAID76
UPC 621945490482

Dimensions

Bolt Size 1/4 in

Certifications And Compliance

Certification - ETL No
Certified Listed UL2703
Industry Standard(s) UL2703

Logistics

Carton Quantity 25
Pallet Quantity 2250

Product Assets

[Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50082227](#)
[Specifications - WILEYBRAID76](#)