

Substation - Copper Expansion Coupler

By Burndy
Catalog # [XP1919HC](#)



Substation Connectors.

Application

Substation

General

Catalog Number	XP1919HC
Connector Type	Couplers
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Type	Tube to Tube Couplers
UPC	781810242865
UPC 12 Digit	7818102428655

Dimensions

Dimension - B Length inch	4.00 in
Dimension - Height inch	8.50 in
Dimension - Height mm	215.9 mm
Dimension - L Length Overall mm	330 mm
Dimension - Length BB inch	4.00 in

Dimension - Length Overall inch	13.00 in
Dimension - Width inch	5.25 in
Dimension - Width mm	133 mm

Conductor Related

Conductor - Connection Combination	Tube to Tube
Conductor - Copper Tube Std Size	2 1/2 IPS
Conductor - Copper Tube Std Size Range	2 1/2 IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - XP1919HC](#)