



Vinyl Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [TP1414](#)

Copper Terminal, Ring Tongue, 16-14 AWG, 1/4" Stud, Vinyl Insulated, Tin Plated.



Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Color Code	Blue
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810713044
UPC 12 Digit	7818107130444

Dimensions

Cable Insulation Diameter Maximum	0.19 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.05 in
Dimension - Pad Width inch	0.40 in
Dimension - Strip Length inch	13/64 in
Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.36 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[3D Models - TP1414_MODEL-PDF](#)
[3D Models - TP1414_MODEL-STEP](#)
[3D Models - TP1414_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_TP1010_LineArt](#)
[Sales Drawings - 50093722](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-TP1414-SPEC-EN | REV 5/2024

