

Y2C6CR, Compression Splice Reducer, Barrel A #2 AWG, Barrel B #6 AWG



By Burndy
Catalog # Y2C6CR

2 AWG CU Long Barrel Size Reduced Down To 6 AWG Wire Size, Internal Chamfer, Tin Plated, Up to 35kV, BROWN Color Code, 10 Die Index.

Features

Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

Application

Wire Reducing Splice Adapter Insert

General

Catalog Number	Y2C6CR
Color Code	Brown
Connector Type	LONG BARREL
Die Index	10
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
UPC	781810098554
UPC 12 Digit	7818100985544

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Inside Diameter inch	0.2 in
Dimension - Outside Diameter inch	0.293 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	2 AWG
Conductor - Copper Str Run Range	250 kcmil
Conductor - Copper Str Size Range	6 AWG
Conductor - Copper Str Tap	6 AWG
Conductor - Copper Str Tap Range	4 AWG
Conductor - Material	COPPER
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..016040-01](#)
[Specifications - Y2C6CR](#)