



# Vinyl Ring Terminal For 22 - 16 AWG

By Burndy  
Catalog # TP1614



Terminal-Polyvinylchloride Insulated, Ring Tongue, 22-16 Max. Insul.Dia. Accom.: .145 Color Code:Red, 12, 1/4, 0.99 in L, .40 in W.

## Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

## General

Color Code	Red
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810715048
UPC 12 Digit	7818107150488

## Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Bolt Size fraction	1/4
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	0.99 in
Dimension - Pad Width inch	0.40 in
Dimension - Strip Length inch	13/64
Dimension - Stud Size inch	1/4
Dimension - Z (inch)	0.36 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Solid Size	18 AWG;17 AWG;16 AWG
Conductor - Copper Solid Size Range	18 AWG-16 AWG
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG
Conductor - Copper Str Size Range	20 AWG - 16 AWG
Conductor Size	22 - 16 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_TP1010\\_LineArt](#)  
[Sales Drawings - 50093722](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-TP1614-SPEC-EN | REV 5/2024

