

# TP168BF, Vinyl Block Fork Terminal For 22 - 16 AWG

By Burndy  
Catalog # TP168BF



Vinyl Block Fork Terminal For 22 - 16 AWG.

## Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

## Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

## General

Catalog Number	TP168BF
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Tongue Type	Block Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	VINYLUG™
Type	Fork Tongue
UPC	781810524398
UPC 12 Digit	7818105243988

## Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	24 mm

Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	13/64 in
Dimension - Stud Size inch	#6 - #8
Dimension - Z (inch)	0.32 in

## Conductor Related

Conductor Range	#22 AWG to #18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_TP166BF\\_LineArt](#)
- [Sales Drawings - 50094181](#)
- [Specifications - TP168BF](#)