

UC4W28, Copper Parallel Groove Clamp

By Burndy
Catalog # UC4W28



CU Parallel Groove Clamp accommodates large number of CU Conductors, Conductor: 4 Sol. - 4/0 Str. (Either Groove).

Features

- Type UC connector accommodates large range of conductors in either groove, reducing inventory requirements
- Interlocking finger design provides firm grip with maximum contact length
- High strength, corrosion resistant silicon bronze hardware

Application

For Range Of Copper

General

Catalog Number	UC4W28
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Plated	N
Plating Type	Unplated
Sub Brand	TAPIT
Type	UC
UPC	781810012888

Dimensions

Dimension - B Length fraction	2-1/8 in
Dimension - B Length inch	2.125 in
Dimension - Height fraction	1-15/16 in
Dimension - Height inch	1.93 in
Dimension - Height mm	50.8 mm
Dimension - Width fraction	1-3/4 in

Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4 AWG
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0

AWG;4/0 AWG

Conductor - Copper Str Size A	4 - 4/0
Conductor - Copper Str Size A Range	4 - 4/0
Conductor - Copper Str Size B	4 - 4/0
Conductor - Copper Str Size B Range	4 - 4/0
Conductor - Copper Str Size Range	4 AWG-4/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [3D Models - UC4W28_MODEL-IGES](#)
- [3D Models - UC4W28_MODEL-PDF](#)
- [3D Models - UC4W28_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_UC_PARA_CLAMP_LineArt](#)
- [Sales Drawings - SA..038990-01](#)
- [Specifications - UC4W28](#)