



UCK2UL, Interlocking-finger Parallel Clamp, #6 AWG Sol/Str Cu, 1/4"-5/16" Galvanized Steel Guy Wire, Tin-Plated Copper

By Burndy
Catalog # [UCK2UL](#)



ACCOM: #6 AWG SOL/STR CU 1/4"- 5/16" GALV. STL GUY
WIRE TORQUE: 110 in-lbs; DURIUUM™ Silicon Bronze Hardware;
Tin-plated, copper.

General

Catalog Number	UCK2UL
Installation Torque	180 LBS/in
Recommended in-lb	
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810120828
UPC 12 Digit	7818101208288

Dimensions

Dimension - Height fraction	1-7/16 in
Dimension - Height inch	1.4375 in
Dimension - Height mm	36.5 mm
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1 in
Dimension - Width fraction	1-7/16 in
Dimension - Width inch	1.4375 in
Dimension - Width mm	37 mm

Conductor Related

Conductor - Copper Solid Size B	6 Sol
Conductor - Copper Str Size B	6 Str

Conductor - Galvanized Steel 1/4 in -5/16 in
Str Size Range

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	150
Minimum Pack Quantity	1
Pallet Quantity	14400

Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_UCK_LineArt](#)
- [Sales Drawings - SD..210746-01](#)
- [Specifications - UCK2UL](#)