



UHR133, Substation Copper Bus Support, 6 Str AWG-500 kcmil, Copper Pipe: 1/8"-1/2" IPS, 3" Bolt Dia

By Burndy
Catalog # UHR133



Cast Cu Alloy Bus Support, CU Str. Size: 6 AWG - 500 Kcmil, CU Pipe Size: 1/8"-1/2" IPS, 3 IN Bolt Circle Dia.

Application

Substation

General

Connector Type	Bus Support
Fitting Type	Rigid Conduit
Hardware Type	Cap mounting kit (w/o nuts)
Installation Torque Recommended in-lb	240 in-lb
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	1/2 X 1" Hot Dipped Galv. Steel Hex. Head Bolts
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810004579
UPC 12 Digit	7818100045799

Dimensions

Bolt Circle Diameter	3 in
Dimension - B Length fraction	3-5/8 in
Dimension - B Length inch	3.56 in
Dimension - G inch	1.75 in
Dimension - Height fraction	3 in
Dimension - Height inch	3.00 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm

Conductor Related

Conductor - Connection Combination	Base to Tube or Cable
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	6 AWG-500 kcmil
Conductor - Copper Tube Std Size	1/8 IPS;1/4 IPS;3/8 IPS;1/2 IPS
Conductor - Copper Tube Std Size Range	1/8 IPS-1/2 IPS
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_UHR_LineArt](#)
[Sales Drawings - sa039220-01](#)



A proud member of the Hubbell Family.