

# Substation - Copper V Type T Connector

By Burndy  
Catalog # [VTT3434](#)



V Style Connectors.

**Features**

- High copper alloy T-Connector for pipe cable, cable tap
- DURIMUM V-Bolt clamping elements accommodate large range of cable are are particularly suited for extra flexible cable
- Twin V elements for additional joint strength against vibration and flexing on tap side

**Application**

Substation

**General**

Catalog Number	VTT3434
Connector Type	T-Connector
Material	Copper Alloy
Material - Hardware	DURIMUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Type	Bolted Tees
UPC	621945153431
UPC 14 Digit GTIN	00621945153431

**Dimensions**

Dimension - Height inch	3.34 in
Dimension - Height mm	84.8 mm
Dimension - L Length Overall mm	133 mm

Dimension - Length Overall inch	5.25 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm

**Conductor Related**

Conductor - Connection Combination	Cable to Cable
Conductor - Copper Str Run	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	300 kcmil-500 kcmil
Conductor - Copper Str Tap	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Tap Range	300 kcmil-500 kcmil

**Certifications And Compliance**

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX

**Logistics**

Minimum Pack Quantity	1
-----------------------	---

**Product Assets**

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - sa004362-01](#)  
[Specifications - VTT3434](#)