


Substation - Copper V Type T Connector

By Burndy
Catalog # [VTT4028](#)



V Style Connectors.

Application

Substation

General

Connector Type	T-Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Type	Bolted Tees
UPC	781810120095
UPC 12 Digit	7818101200955

Dimensions

Dimension - Height inch	2.56 in
Dimension - L Length Overall mm	130 mm
Dimension - Length Overall inch	5.13 in
Dimension - Width inch	1.69 in
Dimension - Width mm	43 mm

Conductor Related

Conductor - Connection Combination	Cable to Cable
Conductor - Copper Solid Tap	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Tap Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Run	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Run Range	500 kcmil-800 kcmil
Conductor - Copper Str Tap	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	1/0 -4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sa004362-01](#)