



## WILEY-RLJ6C6-14, 6 IN L, 1/4 IN Hardware NOT included

By Burndy

Catalog # [WILEY-RLJ6C6-14](#)

Wiley Rope-Lay Bonding Jumper; 1/4" Stud; 6" Length.



### Features

- Bond moving and stationary components with extremely flexible conductor stranding
- Standard mounting geometry and hardware requirements allow quick and easy installation
- Tin plated copper construction ensures durability against the elements and provides the environmental stability required for installation longevity
- Offered in a variety of lengths and mounting hardware sizes - customer configurations available upon request
- Listed to UL467 and UL2703

### Application

The Wiley Rope Lay Jumper is the optimal solution for bonding applications involving moving components. The WILEY-RLJ type jumpers are flexible in all directions and can be mounted to any flat surface. Made from tin plated copper stranding and crimped into a high-quality BURNDY lug, the rope lay jumper meets requirements of both UL467 and UL2703. At a size equivalent to #6 AWG conductor, engineers and installers can be confident in meeting or exceeding bonding requirements in most applications. The WILEY-RLJ jumpers are available with a variety of mounting hole sizes and in three standard lengths. Adding flexibility to both the installation process and application requirements, custom lengths and mounting configurations are available upon request.

### General

Catalog Number WILEY-RLJ6C6-14  
UPC 621945553385

### Dimensions

Bolt Size 1/4 in  
Length 6 in

### Conductor Related

Conductor Size #6 AWG

### Certifications And Compliance

Certified Listed UL2703  
Industry Standard(s) UL2703

### Product Assets

[Catalog Page - BURNDY WileyRopeLayJumper CatCut](#)  
[Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Certifications - Certificate of Compliance, UL 467](#)  
[Certifications - Certificate of Compliance, UL 2703](#)  
[Sales Drawings - 50101194](#)  
[Specifications - WILEY-RLJ6C6-14](#)