

Substation - Copper Expansion Coupler

By Burndy
Catalog # XP1919



Cast Copper Alloy Expansion Coupler , 2-1/2 IN IPS, 13.00 IN L.

Application

Substation

General

Catalog Number	XP1919
Connector Type	Couplers
Installation Torque	480 in-lb
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Type	Tube to Tube Couplers
UPC	781810005057
UPC 12 Digit	7818100050577

Dimensions

Dimension - Height inch	8.50 in
Dimension - L Length Overall mm	330 mm
Dimension - Length BB inch	4.00 in
Dimension - Length Overall inch	13.00 in

Conductor Related

Conductor - Connection Combination	Tube to Tube
Conductor - Copper Tube Std Size	2 1/2 IPS
Conductor - Copper Tube Std Size Range	2 1/2 IPS
Conductor Type	CU Tube Std-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_XP_LineArt](#)
- [Sales Drawings - 50000157](#)
- [Specifications - XP1919](#)