



Electric Hydraulic Pump for use with all HYPRESS™ remote crimpers and cutters requiring 10,000 psi operating pressure, 100,000 (+) life cycles

By Burndy
Catalog # Y10AC9



Pump, 10K psi.

Features

- Easy to carry and transport
- Factory set relief valve
- 100,000+ life cycles
- Sealed electric pendant switch with 10-foot cord

Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
EU RoHS Indicator	Yes
Power Source	5/8 HP 115V-AC Motor; 10000 RPM
Sub Brand	HYPRESS
Tool Type	Pump, Electric Hydraulic
Type	Pumps
UPC	781810467299
UPC 12 Digit	7818104672999

Dimensions

Dimensions	8.25 in x 6.50 in x 14.38 in
Height	14.38 in
Length	8.25 in
Weight	28 lb
Width	6.5 in

Electrical Ratings

Current Draw Max	11 Amperes
------------------	------------

Certifications And Compliance

Standards - RoHS Compliance EX Status

Logistics

Minimum Pack Quantity	1
Package Contents	Pump only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Safety Operating & Maintenance](#)
[Instructions Y10AC9, Y10AC9WC](#)
[Product Cross Section Image\(s\) - BUR_082_OWMF_Y10AC9_lineart](#)
[Sales Drawings - 10089397](#)



A proud member of the Hubbell Family.