



# 12-Ton C-Head Crimper, Self Contained Hydraulic, Uses U Dies, #14 AWG-750 kcmil Copper, #8 AWG-750 kcmil Aluminum, #4 AWG-556.5 kcmil ACSR

By Burndy  
Catalog # Y750HSXT



12T C-Head Crimper, #14-750 kcmil CU, #8-750 kcmil AL, #4-556.5 kcmil ACSR.

## Features

- Easy tool positioning with its 355 head rotation
- Patented rapid advance pump for faster crimps
- Comfort grip handles
- Audible "pop-off" pressure relief valve
- Handle drain trigger

## Application

Crimping

## General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	<ul style="list-style-type: none"> <li>• Crimper</li> <li>• Crimper</li> </ul>
UPC	781810458600
UPC 12 Digit	7818104586000

## Dimensions

Dimensions	23.96 in x 8.71 in x 2.86 in
Height	2.86 in
Jaw Width	1.65 in
Length	23.96 in
Weight	17.2 lb
Width	8.71 in

## Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil
-----------------	-----------------------------------------------------------------------------------------------

## Certifications and Compliance

Standards - RoHS Compliance EX Status

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Plastic Case

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 10076340](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-Y750HSXT-SPEC-EN | REV 1/2024