

# YA34A3UG, 500 kcmil, Aluminum, 2 Hole, 1/2 Stud, 1-3/4 Spacing, AL9CU



By Burndy  
Catalog # [YA34A3UG](#)

AL Terminal, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.

## Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

## Application

Wire Termination

## General

Catalog Number	YA34A3UG
Color Code	Pink
Connector Type	LONG BARREL
Die Index	300
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	ALUMINUM
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Bright Tin Plate
Sub Brand	TERMINALS, HYLUG
Temperature Rating	194
Trade Name	HYLUG™

UPC

750931281947

## Dimensions

Dimension - B Length fraction	2-5/16 in
Dimension - B Length inch	2.34 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	3.15 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	173 mm
Dimension - Length Overall inch	6.80 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.32 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2 5/8
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Thread Size	1/2
Dimension - Z (inch)	0.77 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - AL Str Size	500 KCMIL
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 KCMIL
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	ALUMINUM / COPPER
Conductor Size	500 KCMIL
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B

Standards - Industry Standards Met	UL 486A-486B
UL Listed	Yes

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YA34A3UG-SPEC-EN | REV 9/2024