


YA31L2NT38FX, Compression Terminal, 250 kcmil K, M, 262 DLO, Cu, 2-Hole, 3/8" Stud, 1" Spacing, Narrow Tongue



By Burndy
Catalog # [YA31L2NT38FX](#)

250 kcmil I, K, M, 262 DLO CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Narrow Tongue, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, White Color Code, 17 or 298 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

General

Catalog Number	YA31L2NT38FX
Color Code	White
Connector Type	STANDARD BARREL
Die Index	17
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810246511

Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38

Dimension - D inch	1.84 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	89 mm
Dimension - Length Overall inch	3.51 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.43 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	262 KCMIL
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	250 KCMIL
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex K Size	250 KCMIL
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex M Size	250 KCMIL

Conductor - Copper Flex M Size Range	250 kcmil
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	FLEX
Wire Size	250 KCMIL

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM

UL Listed Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	9250

Product Assets

- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YAL2NTFX_Lineart](#)
- [Sales Drawings - 30003952](#)
- [Specifications - YA31L2NT38FX](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

