

YA6CL2TC14E2SL, Compression Terminal, #6 AWG, 2-Hole, 1/4" Stud, 3/4" Spacing, Standard Barrel

By Burndy

Catalog # [YA6CL2TC14E2SL](#)



Cu Compression Terminal, Slotted, 2 Holes W/InspWindow, #6 AWG, 1/4" Stud, 0.75" Spacing, Standard Barrel.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

General

Catalog Number	YA6CL2TC14E2SL
Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	7
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810175224
UPC 12 Digit	7818101752244

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm

Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.47 in
Dimension - N inch	0.31 in
Dimension - Pad Width inch	0.45 in
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.33 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	50

Product Assets

Catalogs - BURNDY Master Catalog - Section C - Compression
Connections
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - SE212222-01
Specifications - YA6CL2TC14E2SL
Video - HYDENT Compression Terminal Overview Video



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA6CL2TC14E2SL-SPEC-EN | REV 10/2024