



# Uninsulated Ring Terminal For 4/0 AWG

By Burndy  
Catalog # [YAD28M16E58](#)



Uninsulated Ring Terminal For 4/0 AWG.

### Application

The YAD uninsulated OEM lug terminal is constructed of electrolytic copper

### General

Connector Type	Ring Terminal
EU RoHS Indicator	No
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810549568
UPC 12 Digit	7818105495688

### Dimensions

Dimension - B Length inch	0.87 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.67 in
Dimension - L Length Overall mm	62 mm
Dimension - Length Overall inch	2.44 in
Dimension - Outside Diameter inch	0.89 in
Dimension - Pad Width inch	1.10 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	5/8

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>CU C Str-Size</li><li>CU C Flex-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	250
Minimum Pack Quantity	25

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YAD36M20E34\\_LineArt](#)  
[Sales Drawings - 50013661](#)



A proud member of the Hubbell Family.